



MSR Gold™ MiniFastFit (DJ/Club)

MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information					
Cap-Base	PGJX28 [PGJX28]				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Main Application	Entertainment				
Life To 50% Failures (Nom)	750 h				
System Description	MiniFastFit				
Light Technical					
Color Code	2				
Luminous Flux (Min)	21000 lm				
Luminous Flux (Nom)	23000 lm				
Chromaticity Coordinate X (Nom)	288				
Chromaticity Coordinate Y (Nom)	306				
Correlated Color Temperature (Nom)	9300 K				
Luminous Efficacy (rated) (Nom)	77 lm/W				
Color Rendering Index (Nom)	80				

Operating and Electrical					
Power (Rated) (Nom)	300 W				
Lamp Current (Nom)	3.8 A				
Ignition Supply Voltage (Min)	207 V				
Controls and Dimming					
Dimmable	Yes				
Mechanical and Housing					
Cap-Base Information	PGJX28				
Luminaire Design Requirements					
Bulb Temperature (Max)	950 °C				
Pinch Temperature (Max)	500 °C				
Product Data					
Full product code	871829122111100				

Datasheet, 2017, January 30 data subject to change

MSR Gold™ MiniFastFit (DJ/Club)


Order product name	MSR Gold™ 300/2 MiniFastFit 1CT/4				
EAN/UPC - Product	8718291221111				
Order code	928177105115				
Numerator - Quantity Per Pack	1				
Numerator - Packs per outer box	4				

Material Nr. (12NC)	928177105115
Net Weight (Piece)	0.062 kg

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



MSR GOLD 300/2 MiniFastFit

Product	D	0	L	L	L	С
MSR Gold™ 300/2 MiniFastFit	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm
1CT/4						

